

GLOBAL BLOWER & DRUM FANS



Features	Family	Direct Drive	Belt Drive
<p>Industrial Portable Blower Fans Feature A Quiet 2-Speed Motor With Thermal Cutoff For Overheat Protection. Industrial Portable Blower Fans provide a roller bearing motor for heat resistant and maintenance-free operation. Sturdy steel housing has formed channels for enhanced rigidity and a powder coat black finish for long lasting durability. Portable fans include a grip handle for easy transport. Grills have curved grid supports and include an 18'L 3-conductor power cord with plug. Direct Drive Fans feature 3 blades that allows blower tilt to direct airflow vertically. Includes two wheels for mobility. Belt Driven Fans have 4 balanced blades and solid rubber wheels for mobility. Meets OSHA standards, UL listed. Includes 1 Year Limited Warranty. model 246607 features a full 360° orbital rotation.</p>	Models	292607, 292594, 607220, 246607, 246556, 258320	246558, 246559, 600554, 600555
	Fan Sizes Available	18", 24", 30", 36"	36", 42", 48"
	Motor HP Ratings	1/40, 1/4, 1/3, 2/3	1/3, 1/2, 1, 1-1/2