



Valley Craft's economical, adaptable drum dumpers are available in Single-Stage Low-Level and Dual-Stage High-Level capacities. With user safety as our number one priority, versatile product features include:

Single Stage, Low Level models

- 1,000-lb and 1,500-lb capacity models; Stationary and Portable models
- Handles containers up to 24" in diameter
- 1/60/110V Power unit is equipped with a 1HP motor and a 1GPM pump
- 45° maximum dumping angle
- Rotary switch control to power chute up
- Gravity down system with adjustable flow control to safely lower chute
- Adjustable hold-down bar keeps container from shifting
- Heavy-gauge carbon steel construction with powder coat finish
- Includes corded hand control box with magnetic back

Stationary

Load Capacity	1,000 lbs			1,500 lbs		
Part Number	F80169A9	F80167A7	F80165A5	F80163A3	F80161A1	F80159A9
Name	36" Low level	48" Low level	60" Low level	36" Low level	48" Low level	60" Low level
Weight	363 lbs	404 lbs	446 lbs	660 lbs	690 lbs	720 lbs
Width	36"	36"	36"	36"	36"	36"
Length	52"	52"	52"	52"	52"	52"
Frame Height	58.5"	65.5"	72.5"	58.5"	65.5"	72.5"
Dump Height	36"	48"	60"	36"	48"	60"
Overhead Clearance	96.5"	112.5"	129.5"	96.5"	112.5"	129.5"
Chute Reach	11"	9"	7"	11"	9"	7"
Horizontal Clearance	60"	68"	76"	60"	68"	76"
Cycle Time (Up Only)	25 sec	25 sec	25 sec	25 sec	25 sec	25 sec

Portable

Load Capacity	1,000 lbs			1,500 lbs		
Part Number	F80168A8	F80166A6	F80164A4	F80162A2	F80160A0	F80158A8
Name	36" Low level	48" Low level	60" Low level	36" Low level	48" Low level	60" Low level
Weight	413 lbs	510 lbs	496 lbs	510 lbs	530 lbs	563 lbs
Width	36"	36"	36"	36"	36"	36"
Length	52"	52"	52"	52"	52"	52"
Frame Height	59.5"	66.5"	73.5"	59.5"	66.5"	73.5"
Dump Height	37"	49"	61"	37"	49"	61"
Overhead Clearance	97.5"	113.5"	130.5"	97.5"	113.5"	130.5"
Chute Reach	11"	9"	7"	11"	9"	7"
Horizontal Clearance	60"	68"	76"	60"	68"	76"
Cycle Time (Up Only)	25 sec	25 sec	25 sec	25 sec	25 sec	25 sec

Drum Dumpers



Dual Stage, High Level models

- Stationary and Portable models; 1,500-lbs capacity
- Handles containers up to 24" in diameter
- Chute rises vertically until arms meet pivot rollers, causing chute to rotate
- 1/60/110V Power unit is equipped with a 1HP motor and a 1GPM pump
- 45° maximum dumping angle
- Rotary switch control to power chute up
- Gravity down system with adjustable flow control to safely lower chute
- Adjustable hold-down bar keeps container from shifting
- Heavy-gauge carbon steel construction with powder coat finish
- Includes corded hand control box with magnetic back

Stationary

Load Capacity	1,500 lbs				
Part Number	F80157A7	F80155A5	F80153A3	F80151A1	F80149A9
Name	72" High level	84" High Level	96" High Level	108" high Level	120" High Level
Weight	1,125 lbs	1,160 lbs	1,200 lbs	1,235 lbs	1,475 lbs
Width	36"	36"	36"	36"	36"
Length	47"	47"	47"	47"	47"
Frame Height	86"	98"	110"	122"	134"
Dump Height	72"	84"	96"	108"	120"
Overhead Clearance	131"	143"	155"	167"	179"
Chute Reach	6.5"	6.5"	6.5"	6.5"	6.5"
Horizontal Clearance	66"	66"	66"	66"	66"
Cycle Time (Up Only)	58 sec	68 sec	78 sec	88 sec	98 sec

Portable

Load Capacity	1,500 lbs				
Part Number	F80156A6	F80154A5	F80152A2	F80150A0	F80148A8
Name	72" High Level	84" High Level	96" High Level	108" high Level	120" High Level
Weight	1,125 lbs	1,160 lbs	1,200 lbs	1,235 lbs	1,475 lbs
Width	36"	36"	36"	36"	36"
Length	51"	51"	51"	51"	51"
Frame Height	87"	99"	111"	123"	135"
Dump Height	73"	85"	97"	109"	121"
Overhead Clearance	132"	144"	156"	168"	180"
Chute Reach	6.5"	6.5"	6.5"	6.5"	6.5"
Horizontal Clearance	66"	66"	66"	66"	66"
Cycle Time (Up Only)	58 sec	68 sec	78 sec	88 sec	98 sec